



SECTION III: RUNNING TOOLS

Type 'BR' Soft Release Running Tool Assembly: 1.900" – 3 1/2"

Rebco Type 'BR' Soft Release Running Tool is designed to run and set recording instruments (see [Product Code 33](#)), attached to Type 'ROTS', Type 'ROTW' and Type 'ROTZ' Locks to be landed in corresponding Nipple profiles.

Type 'ROTTs' Lock is to be set in the Tubing Coupling recess. This tool is an up strain, slack-off setting device.

NOTE: Jarring with this tool should be avoided, as it may cause the tool to be released prematurely.

It is recommended that Type 'BR' Soft Release Running Tool is run on Stem or Knuckle Jars only.



TECHNICAL DATA

NOMINAL SIZE	1.900"	2 3/8"	2 7/8"	3 1/2"
ASSEMBLY NUMBER	4101131900	4101132370	4101132870	4101133500

ENGINEERING DATA:

MAXIMUM OD	1.406"	1.688"	2.094"	2.625"
PIN THREAD CONNECTION	15/16" - 10	15/16" - 10	15/16" - 10	1 1/16" - 10
FISHING NECK OD	1.187"	1.375"	1.750"	2.313"
LENGTH	15.56"	14.75"	17.38"	18.12"
MATERIAL	Alloy	Alloy	Alloy	Alloy

Note¹ Locks Type: 'ROTS' and 'ROTTs'

- Locks must be run with (up-facing) Dogs trailing.
- Require 'ROTA' Shank to collapse down-facing Dogs.
- Pull required to activate the Tool: 100 to 150 lbs

Locks Type: 'ROTW' and 'ROTZ'

- Do not use 'ROTA' Shank
- Pull required to activate the Tool: 180 lbs for 1.900" and 300 lbs for other sizes
- For Type 'ROTA' Shanks see [PRODUCT CODE 49](#), Section II: SERVICE TOOLS